


Nov.1.2019 Copyright 2019 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- 1 This product is delivered disassembled.
 - 2 Applicable crimp contact:
Contact No.1 to 11 : RP13A-SC-222(CL113-0151-0)
(Wire range, AWG #24 to 28 , Jacket diameter ϕ 1.4Max.)
Contact NO.12 to 13 : RP13A-SC-212(CL113-0150-8)
(Wire range, AWG #18 TO 22 , Jacket diameter ϕ 1.9Max.)
 - \triangle 3 Applicable crimp contact crimping tool: RP13A-TC-01(CL150-0070-0)
Applicable crimp contact extraction tool: RP13A-SC-TP(CL150-0022-8)
 - \square 4 The recommended clamp torque of Ref.No. ⑦ to 0.2 N·m.
 - 5 The cable pull and twisting strength and other characteristics may differ.
Depending on the cable structure, please confirm before the use.

4	Brass				
3	Polycarbonate	(Black) UL94V-0	7	Brass	ZINC PLATING BLACK CHROMETE TREATMENT (TRIVALENT CHROMIUM) JIS B 1111 M2X0.4X4
2	Polycarbonate	(Black) UL94V-0	6	Steel	Chromate treatment
1	Polycarbonate	(Black) UL94V-0	5	Flexible polyvinylchloride	(Black)
部番	材 質	处 理 , 備 考	部番	材 質	处 理 , 備 考

UNITS mm	\odot ∇	SCALE 2 : 1	\triangle 1	訂 正 記 事 DIS-C-00001221	設 計 MM. ISHII	検 図 EJ. KUNII	年 月 日 16.10.18
-------------	------------------	----------------	---------------	---------------------------	------------------	------------------	-------------------

HRS HIROSE ELECTRIC CO., LTD.	承 認 : EJ. KUNII	16.05.17	図 番 :	EDC-009285-71-00
	検 図 : EJ. KUNII	16.05.17	製 品 名 :	RP13A-12P-13SC(71)
	設 計 : MM. ISHII	16.05.17	製 品	CL113-0149-9-71
	製 図 : MM. ISHII	16.05.17	コ ー ド	