


Sep.1.2019 Copyright 2019 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- 1 Applicable crimping contact: RP19-SC-222(CL113-0266-2)
(Applicable wire: AWG #24 to 30)
 - 2 Applicable crimp contact extraction tool: RP6-SC-TP(CL150-0039-0)
 - 3 This product is delivered disassembled.
 - 4 The cable pull and twisting strength and other characteristics may differ,
Depending on the cable structure. please confirm before the use.

4	Brass					
3	Polycarbonate	(Black)	UL94V-0	7	Flexible polyvinylchloride	(Black)
2	Polycarbonate	(Black)	UL94V-0	6	Brass	Black chromate treatment(Trivalent chromium) JIS B1111 M2×0.4×4
1	Polycarbonate	(Black)	UL94V-0	5	Steel	Nickel plating
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS

UNITS mm	SCALE 2 : 1	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.			APPROVED :EJ. KUNII CHECKED :EJ. KUNII DESIGNED :MM. ISHII DRAWN :MM. ISHII	16.05.17 16.05.17 16.05.17 16.05.17	DRAWING NO. PART NO. CODE NO.	EDC-021588-71-00 RP13A-12PG-20SC(71) CL113-0210-8-71
						1/1