


Jan.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




NOTES: 1

APPLICABLE CABLE


VINYL SEATH	( Ø5 )	DRAIN WIRE	WIRE	INSULATOR OUTER DIAMETER	0.90 TO 1.00 DIA.
FILLER		WIRE		CONDUCTOR SIZE (STRANDED)	AWG26~27 OR EQUIVALET
CONDUCTOR		INSULATOR	VINYL SEATH OUTER DIAMETER	Ø5.0	*(1)
		SHIELD	DRAIN WIRE	AWG 25 OR EQUIVALENT	7/0.18 DIA. *(2)

\*(1)CABLE ENTRY IS 5.6 MIN.  
\*(2)CONSTRUCTION IS FOR REFERENCE.

HOOD(2:1)



ADAPTER



2 ADAPTER SHALL BE USED TO ALIGN INDIVIDUAL WIRE.  
3 THE DIMENSION IN PARENTHESIS IS FOR REFERENCE.

2	PHOSPHOR BRONZE	UNDER :NICKEL PLATING 2µm min OVER :GOLD PLATING 1.27µm min	5	POLYCARBONATE	LIGHT BEIGE
1	POLYCARBONATE	TRANSPARENCY	4	POLYCARBONATE	TRANSPARENCY
			3	BRASS	UNDER :COPPER PLATING 0.5µm min OVER :TIN REFLOW PLATING 1µm min
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS	mm	SCALE	4 : 1	COUNT	3
DESCRIPTION OF REVISIONS		DESIGNED	YH.MAMADA		
DIS-E-003517		CHECKED	YH.ENAMI		
APPROVED :HO.MIWA 05.01.05		DATE	10.11.26		
CHECKED :TH.KAMEYA 05.01.05		DRAWING NO.	EDC3-120679-00		
DESIGNED :SS.SATO 05.01.05		PART NO.	TM11AP-88P		
DRAWN :SS.SATO 05.01.05		CODE NO.	CL222-2780-6-00		
HRS HIROSE ELECTRIC CO., LTD.		1/1			