


Jan.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTES: 1

APPLICABLE CABLE

VINYL SEATH	(Ø 5)	DRAIN WIRE		INSULATOR OUTER DIAMETER	0.90 TO 1.00 DIA.
		WIRE	WIRE	CONDUCTOR SIZE (STRANDED)	AWG26~27 OR EQUIVALET
FILLER				VINYL SEATH OUTER DIAMETER	Ø5.0 *(1)
CONDUCTOR		INSULATOR		DRAIN WIRE	AWG 25 OR EQUIVALENT
		SHIELD			7/0.18 DIA. *(2)

*(1)CABLE ENTRY IS 5.6 MIN.

*(2)CONSTRUCTION IS FOR REFERENCE.

ADAPTER

② ADAPTER SHALL BE USED TO ALIGN INDIVIDUAL WIRE.

3 THE DIMENSION IN PARENTHESIS IS FOR REFERENCE.

2	PHOSPHOR BRONZE	UNDER :NICKEL PLATING 2µm min OVER :GOLD PLATING 1.27µm min	4	POLYCARBONATE	TRANSPARENCY
1	POLYCARBONATE	TRANSPARENCY	3	BRASS	UNDER :COPPER PLATING 0.5µm min OVER :TIN REFLOW PLATING 1µm min
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS	mm	SCALE	4 : 1	COUNT	3
		DESCRIPTION OF REVISIONS		DESIGNED	YH. MAMADA
		DIS-E-003517		CHECKED	YH. ENAMI
		DATE		10.11.26	
APPROVED : HO. MIWA		05.01.05		DRAWING NO. EDC3-120679-01	
CHECKED : TH. KAMEYA		05.01.05		PART NO. TM11AP-88P(01)	
DESIGNED : SS. SATOH		05.01.05		CODE NO. CL222-2780-6-01	
DRAWN : SS. SATOH		05.01.05			