


Jan.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




NOTES: 1

APPLICABLE CABLE


VINYL SEATH	(Ø5)	DRAIN WIRE	WIRE	INSULATOR OUTER DIAMETER	0.90 TO 1.00 DIA.
FILLER		WIRE		CONDUCTOR SIZE (STRANDED)	AWG26~27 OR EQUIVALET
CONDUCTOR		INSULATOR	VINYL SEATH OUTER DIAMETER	Ø5.0	*(1)
		SHIELD	DRAIN WIRE	AWG 25 OR EQUIVALENT	7/0.18 DIA. *(2)

*(1)CABLE ENTRY IS 5.6 MIN.
*(2)CONSTRUCTION IS FOR REFERENCE.

HOOD(2:1)



ADAPTER



2 ADAPTER SHALL BE USED TO ALIGN INDIVIDUAL WIRE.
3 THE DIMENSION IN PARENTHESIS IS FOR REFERENCE.

2	PHOSPHOR BRONZE	UNDER :NICKEL PLATING 2µm min OVER :GOLD PLATING 1.27µm min	5	POLYCARBONATE	BLACK
1	POLYCARBONATE	TRANSPARENCY	4	POLYCARBONATE	TRANSPARENCY
			3	BRASS	UNDER :COPPER PLATING 0.5µm min OVER :TIN REFLOW PLATING 1µm min
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS	mm	SCALE 4 : 1	COUNT 3	DESCRIPTION OF REVISIONS	DESIGNED YH.MAMADA
					CHECKED YH.ENAMI
					DATE 10.11.26
APPROVED :HO.MIWA		05.01.05	DRAWING NO. EDC3-120679-06		
CHECKED :TH.KAMEYA		05.01.05	PART NO. TM11AP-88P(03)		
DESIGNED :SS.SATO		05.01.05	CODE NO. CL222-2780-6-03		
DRAWN :SS.SATO		05.01.05			