

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-30°C TO + 85°C (NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO + 60°C (NOTE 2)	
	OPERATING HUMIDITY RANGE \triangle	40% TO + 80%	STORAGE HUMIDITY RANGE \triangle	40% TO + 70% (NOTE 2)	
	VOLTAGE	250V AC	APPLICABLE CONNECTOR	DF3-*S-2C	
	CURRENT	AWG24 : 3A AWG26 : 2A AWG28 : 1A	APPLICABLE CABLE	UL1061, 1007 AWG24 TO 28	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE	100mA (DC OR 1000 Hz).	30m Ω MAX.	X	-	
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 30m Ω MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
CONTACT INSERTION AND EXTRACTION FORCE	\square 0.5 \pm 0.002 BY STEEL GAUGE.	INSERTION FORCE 4.4N MAX EXTRACTION FORCE 0.3N MIN	X	-	
CLIMP TENSILE STRENGTH	MEASURE MAX, VALUE UNDER THE FOLLOWING METHOD: APPLY WIRE TENSILE STRENGTH TO CAULKING AREA AXIALLY UNTIL WIRE BECOME LOOSEN OR BREAKDOWN.	AWG24 35N MIN (11 CORES / 0.16 mm) AWG26 24N MIN (7 CORES / 0.16 mm) AWG28 16N MIN (7 CORES / 0.127 mm)	X	-	
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μ s. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μ s. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 \rightarrow 5 TO 35 \rightarrow 85 \rightarrow 5 TO 35 °C TIME 30 \rightarrow 10 TO 15 \rightarrow 30 \rightarrow 10 TO 15 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 30m Ω MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 \pm 2 °C, 90 TO 95 %, 96 h.	① CONTACT RESISTANCE: 30m Ω MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
REMARKS					
NOTE 1:INCLUDING THE TEMPERATURE RISE BY CURRENT NOTE 2:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD, AFTER PCB BOARD, OPERATINGTEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION.					
\triangle	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	2	DIS-H-002402	AK. MIURA	HK. UMEHARA	07.08.30
Unless otherwise specifid , refer to JIS C 5402.			APPROVED	KJ. KATAYOSE	05.01.05
			CHECKED	TY. OMA	05.01.05
			DESIGNED	IO. DENPOUYA	05.01.05
			DRAWN	IO. DENPOUYA	05.01.05
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-018921-00
HRS	SPECIFICATION SHEET		PART NO.	DF3-2428SCF	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL543-0001-2-00	\triangle 1/1