






5		6		7		8	
訂正記事	担当	年月日	△の数	訂正記事	担当	年月日	△の数
△			△				
△			△				
△			△				



部番	材	質	処	理	備	考	製	図	担	当	接	図	査	理	備	考			
1	ポリブチル樹脂															UL94V-0 (クロ色)			
一般公差							INC 93.9.6 白石	INC 93.9.6 白石	INC 93.9.7 小間	INC 93.9.8 山本	DF11-16DS-2C								
寸法区分							公差												
6以下							±0.3												
6をこえ 18以下							±0.5												
18をこえ 50以下							±0.7												
50をこえ 125以下							±1												
125をこえ 250以下							±1.3												
角 度							±1°												
旧図	CL	-	-	-	-	-											製品名		
旧図	DC3-	-	-	-	-	-											製品名	CL543-0507-1	
図番							ADC3-20803-01										尺 寸	5	mm