





RECOMMENDED CABLE SUBASSEMBLY



B(FREE)




A-A(FREE)



CABLE TERMINATION FIGURE(FREE)

DF36A-25P-SHL or DF36-25P-SHL



- NOTES 1. APPLICABLE CABLE: THIN COAXIAL CABLE(AWG#42~AWG#46)
2. THIS CONNECTOR IS NOT HOT PLUGCABLE. MATE AND UNMATE WHILE THE POWER IS OFF.
3. THE ASSEMBLY IS COMPLETED BY COMBINING TWO PARTS(CONNECTOR UNIT, AND METAL SHIELDING). REFER TO THE TABLE FOR EACH ITEM No, PART NAME, PART No AND CODE No.
APPLICABLE SHELL IS DIFFERENT DEPENDING ON THE PART NO. OF MATED CONNECTOR.
USE DF36A-25P-SHL FOR DF36A-25S-0.4V(**), USE DF36-25P-SHL FOR DF36-25S-0.4V(**).

ITEM No.	PART NAME	PART No.	CODE No.
1,2	CONNECTOR UNIT	DF36-25P-0.4SD(55)	CL662-4006-4-55
-	METAL SHIELDING	DF36A-25P-SHL	CL662-4007-7-00
-	METAL SHIELDING	DF36-25P-SHL	CL662-4012-7-00

4. BLACK MARKS MAY OCCASIONALLY OCCUR IN MOLD RESIN, YET THEY DO NOT AFFECT CONNECTOR QUALITY.

1	PHOSPHOR BRONZE	CONTACT AREA : GOLD PLATING 0.1μm min TERMINATION AREA : GOLD PLATING 0.1μm min UNDER PLATING : NICKEL PLATING 1μm min	5	PS	BLACK
NO.	MATERIAL	FINISH . REMARKS	4	POLYESTER	CLEAR
UNITS mm	SCALE 5 : 1	COUNT △	3	PS	CLEAR
APPROVED : MH. YAMANE	14. 07. 18	DRAWING NO.	2	LCP	UL94V-0, BEIGE
CHECKED : MH. TSUCHIDA	14. 07. 17	PART NO.	NO.	MATERIAL	FINISH . REMARKS
DESIGNED : AH. MIYAZAKI	14. 07. 16	CODE NO.	EDC3-312853-03		
DRAWN : AH. MIYAZAKI	14. 07. 16		DF36-25P-0.4SD(55)		
			CL662-4006-4-55		

