






RECOMMENDED CABLE SUBASSEMBLY


B (30 : 1)



A-A (20 : 1)





CABLE TERMINATION FIGURE (20 : 1)



- NOTES 1. APPLICABLE CABLE: THIN COAXIAL CABLE (AWG#42~AWG#46)
2. THIS CONNECTOR IS NOT HOT PLUGGABLE. MATE AND UNMATE WHILE THE POWER IS OFF.
3. THE ASSEMBLY IS COMPLETED BY COMBINING TWO PARTS (CONNECTOR UNIT, AND METAL SHIELDING).
REFER TO THE TABLE FOR EACH ITEM No., PART NAME, PART No. AND CODE No.

ITEM No.	PART NAME	PART No.	CODE No.
1, 2	CONNECTOR UNIT	DF38B-30P-0.3SD(51)	CL662-4515-8-51
-	METAL SHIELDING	DF38-30P-SHL	CL662-4507-0

			5	PS	BLACK			
			4	POLYESTER	CLEAR			
1	PHOSPHOR BRONZE	CONTACT AREA : Au PLATING 0.1μm min TERMINATION AREA : Au PLATING 0.1μm min UNDER PLATING : Ni PLATING 1μm min	3	PS	CLEAR			
			2	LCP	UL94V-0 , BLACK			
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS			
UNITS mm		SCALE FREE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED : TS. SAKATA	10.08.03	DRAWING NO.	EDC3-320001-01			
		CHECKED : IO. DENPOUYA	10.08.03	PART NO.	DF38B-30P-0.3SD(51)			
		DESIGNED : TP. MATSUMOTO	10.08.03	CODE NO.	CL662-4515-8-51			
		DRAWN : TP. MATSUMOTO	10.08.03	 1/2				



HR5

DRAWING NO.	EDC3-320001-01
PART NO.	DF38B-30P-0.3SD(51)
CODE NO.	CL662-4515-8-51

2/2