

APPLICABLE STANDARD		ANSI/TIA/EIA-568-B.2.10 CAT6a				
RATING	OPERATING TEMPERATURE RANGE	1 -25 °C TO 60 °C		STORAGE TEMPERATURE RANGE	-25 °C TO 60 °C	
	VOLTAGE	125 V AC		OPERATING HUMIDITY RANGE	95 % MAX	
	CURRENT	1 A		APPLICABLE CABLE	—	
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QTAT	
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.			X	X
1 ①THE OPERATION TEMPERATURE INCLUDES THE TEMPERATURE RISE BY CURRENT CARRYING. ②TEMPERATURE RANGE FOR A CONNECTOR UNMATED. ③USE UNDER THE CONDITION RECOMMENDED BY A CABLE MANUFACTURE.						
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
Δ						
REMARK				APPROVED	YH. ENAMI	09. 06. 02
				CHECKED	YH. ENAMI	09. 06. 02
				DESIGNED	MT. ITANO	09. 06. 02
				DRAWN	MT. ITANO	09. 06. 02
Unless otherwise specified, refer to JIS C 5402.						
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-126868-02	
HRS	SPECIFICATION SHEET		PART NO.		TM31P-TM-88P (02)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.		CL222-4626-7-02	Δ 1/1