









RECOMMENDED CABLE SUBASSEMBLY



CABLE TERMINATION FIGURE(30:1)



- NOTES 1. APPLICABLE CABLE: THIN COAXIAL CABLE (AWG#42-AWG#46)
2. THIS CONNECTOR IS NOT HOT PLUGGABLE. MATE AND UNMATE WHILE THE POWER IS OFF.
3. THE ASSEMBLY IS COMPLETED BY COMBINING TWO PARTS "CONNECTOR UNIT AND METAL SHIELDING". REFER TO THE TABLE FOR EACH ITEM No., PART NAME, PART No. AND CODE No.
APPLICABLE SHELL IS DIFFERENT DEPENDING ON THE PART No. OF MATED CONNECTOR.
USE DF36A-20P-SHL FOR DF36A-20S-0.4V(**), USE DF36-20P-SHL FOR DF36-20S-0.4V(**).

ITEM No.	PART NAME	PART No.	CODE No.
1, 2	CONNECTOR UNIT	DF36-20P-0.4SD(55)	CL662-4040-2-55
-	METAL SHIELDING	DF36A-20P-SHL	CL662-4042-8-00
-	METAL SHIELDING	DF36-20P-SHL	CL662-4041-5-00

1		PHOSPHOR BRONZE	CONTACT AREA : GOLD PLATING 0.1μm min TERMINATION AREA : GOLD PLATING 0.1μm min UNDER PLATING : NICKEL PLATING 1μm min	5	PS	BLACK
NO.		MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
UNITS		mm	SCALE	COUNT		DESCRIPTION OF REVISIONS
			5 : 1			DESIGNED
						CHECKED
						DATE
						APPROVED : MH. YAMANE 14. 07. 18
						CHECKED : MH. TSUCHIDA 14. 07. 17
						DESIGNED : AH. MIYAZAKI 14. 07. 16
						DRAWN : AH. MIYAZAKI 14. 07. 16
						DRAWING NO. EDC3-320378-02
						PART NO. DF36-20P-0.4SD(55)
						CODE NO. CL662-4040-2-55

