



Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


A
B
C
D
E
F



PCB LAYOUT FOR REFERENCE(MOUNTING SURFACE SIDE)



TERMINAL No. CHART



■ : PATTERN PROHIBITION AREA

NOTE 5 PANEL THICKNESS IS 1.6mm MAX.

HRS



DRAWING NO.	EDC3-126869-00
PART NO.	DH60A-51P
CODE NO.	CL0244-0043-4-00

6/24

A
B
C
D
E
F

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

DRAWING FOR PACKING(FREE)



※TRAYS, A TYPE AND B TYPE, ARE PILED UP ALTERNATELY.


HR5

DRAWING NO.	EDC3-126869-00
PART NO.	DH60A-51P
CODE NO.	CL0244-0043-4-00

6/3/4

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

△ REFERENCE METAL MASK LAYOUT(2:1)
(t=0.15)



GENERAL TOLERANCE IS ± 0.05

- △ 6. Metal mask dimensions of the drawings described, are reference dimensions for 0.15 mm thickness metal mask.
Change the metal mask dimensions by thickness of the metal mask, thickness of PCB, component of solder paste and mounting conditions.
Change the metal mask dimensions in case of mounting DH**-*P in parallel.
Change the metal mask dimensions, if there are other mounting parts or implementation pattern around the portion of mounting position of DH**-*P.

HRS

DRAWING NO.	EDC3-126869-00
PART NO.	DH60A-51P
CODE NO.	CL0244-0043-4-00