






Technical drawing of a rectangular plate with dimensions and tolerances:

- Overall width: 35.2 ± 0.05
- Overall height: 6.1 ± 0.1
- Distance from top edge to center line: 1.5 ± 0.05
- Distance from bottom edge to center line: 1.45 ± 0.05
- Distance from left edge to center line: 17.6 ± 0.05
- Distance from right edge to center line: 17.6 ± 0.05
- Distance from left edge to first hole center: 0.8 ± 0.05
- Distance from right edge to first hole center: 2 ± 0.05
- Distance from left edge to second hole center: 0.5 ± 0.03
- Distance from right edge to second hole center: 1.3 ± 0.05
- Hole diameter: $\phi 1 \pm 0.05$
- Position of polarization mark: Indicated by a circle with a dot.

- | | | | | | | | | | |
|---|---|-----------------------|---|-----------------|--------------------------------|------------------|---------------------|---------|------|
| 1 | PPS | LIGHT BROWN (UL94V-0) | 2 | PHOSPHOR BRONZE | CONTACT AREA:GOLD 0.1μm min. | | | | |
| | | | | | LEAD AREA:TIN-PLATING 1μm min. | | | | |
| | | | | | UNDER PLATING:NICKEL 2μm min. | | | | |
| NO. | MATERIAL | FINISH . REMARKS | | NO. | MATERIAL | FINISH . REMARKS | | | |
| UNITS
mm |  | SCALE
2 : 1 |  | COUNT | DESCRIPTION OF REVISIONS | | DESIGNED | CHECKED | DATE |
|  HIROSE ELECTRIC CO., LTD. | | APPROVED : HS. OKAWA | 07. 06. 20 | | DRAWING NO. | | EDC3-084984-23 | | |
| | | CHECED : HS. OZAWA | 07. 06. 20 | | PART NO. | | FX6-80S-0. 8SV2(93) | | |
| | | DESIGNED : KT. DOI | 07. 06. 20 | | CODE NO. | | CL576-0127-1-93 | | |
| | | DRAWN : TS. MIYAKI | 07. 06. 14 | | | | | | |
| | | | | | | | | | |

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

