

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C(NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C(NOTES 3)	
	OPERATING HUMIDITY RANGE	20% TO 80%(NOTES 2)	STORAGE HUMIDITY RANGE	40% TO 70%(NOTES 2)(NOTES 3)	
	VOLTAGE		APPLICABLE CONNECTOR	DF81※-30S-0.4H(##)	
	CURRENT		APPLICABLE CABLE		
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QTAT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	XX
MARKING		CONFIRMED VISUALLY.			XX
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARKS NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT NOTE2: NON CONDENSING NOTE3: THE TERM "STORAGE" REFERS TO PRODUCTS STORED FOR A LONG PERIOD PRIOR TO MOUNTING AND USE. THE OPERATING TEMPERATURE AND HUMIDITY RANGE COVERS THE NON-CONDUCTING CONDITION OF CONNECTORS AFTER BOARD MOUNTING AND THE TEMPORARY STORAGE CONDITIONS OF TRANSPORTATION, etc Unless otherwise specified, refer to JIS C 5402,IEC60512.			APPROVED	MH. YAMANE	13. 11. 06
			CHECKED	MH. TSUCHIDA	13. 11. 05
			DESIGNED	AH. MIYAZAKI	13. 11. 01
			DRAWN	AH. MIYAZAKI	13. 11. 01
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-340821-02
HRS	SPECIFICATION SHEET		PART NO.	DF81-30P-LCH (52)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL662-8107-3-52	△ 1/1