

May.1.2020 Copyright 2020 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-25°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +60°C	
	OPERATING&STORAGE HUMIDTY RANGE	85%MAX	APPLICABLE CABLE	CABLE DIAMETER : φ6.4~7.8	
	VOLTAGE		CURRENT		
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	2	DIS-E-00002570	TS. ITO	TU. TANIGUCHI	20191007
REMARK			APPROVED	KN. ICHIKAWA	20100705
THIS PRODUCT SHALL BE MATED WITH DH40-27S OR DH3 * B-27S, IT APPLIES TO DH40-27S OR DH3 * B-27S ABOUT A MECHANICAL, ENVIRONMENTAL CHARACTERISTICS. Unless otherwise specified, refer to IEC 60512.			CHECKED	KN. ICHIKAWA	20100705
			DESIGNED	TU. TANIGUCHI	20100705
			DRAWN	TU. TANIGUCHI	20100705
			Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.
	SPECIFICATION SHEET		PART NO.	DH-27-CV2B	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL244-0014-6-00	1/1