

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-25°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +60°C	
	OPERATING&STORAGE HUMIDTY RANGE	85%MAX	APPLICABLE CABLE	OUTER DIAMETER OF CABLE : $\phi 8.8 \pm 0.5$	
	VOLTAGE	AC 125V			
	CURRENT	0.5 A			
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.		X	X
ELECTRICAL CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).	65 mΩ MAX. (SIGNAL) 	X	X
INSULATION RESISTANCE		100 V DC.	1000 MΩ MIN.	X	—
VOLTAGE PROOF		250 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	X
MECHANICAL CHARACTERISTICS					
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.	INSERTION FORCE 36 N MAX. WITHDRAWAL FORCE 3.3 N MIN.	X	—
MECHANICAL OPERATION		1000 TIMES INSERTIONS AND EXTRACTIONS.	1) CONTACT RESISTANCE 85 mΩ MAX.  2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
VIBRATION		FREQUENCY 10 TO 55 Hz SINGLE AMPLITUDE 0.75 mm, 5 min/CYCLE, TOTAL 10 CYCLES.	1) NO ELECTRICAL DISCONTINUITY OF 10 μs. 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
SHOCK		490 m/s ² DIRECTIONS OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		X	—
ENVIRONMENTAL CHARACTERISTICS					
THERMAL SHOCK		TEMP -55 → +5 TO +35 → +85 → +5 TO +35 °C TIME 30 → 5 → 30 → 5 min. UNDER 5 CYCLES.	1) CONTACT RESISTANCE: 85 mΩ MAX.  2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
HUMIDITY LIFE		TEMPERATURE 40 °C, HUMIDITY 90 TO 95 %, FOR 96 h	1) INSULATION RESISTANCE: 100 MΩ MIN. 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
CORROSION SALT MIST		EXPOSED AT 5 % SALT WATER, FOR 48 h.	NO HEAVY CORROSION THAT LOSE FUNCTION.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
					
REMARK			APPROVED	A0. SUZUKI	10. 03. 23
 EXCLUDES CONDUCTOR RESISTANCE OF CABLE. 2 EXAMINATION IS HELD WITH "DH-37-CV * B", "DH40-37S" AND "DH60-37P" OR "DH-37-CT * B", "DH40-37S" AND "DH60A-37P". Unless otherwise specified, refer to JIS C 5402 .			CHECKED	KN. ICHIKAWA	10. 03. 23
			DESIGNED	TU. TANIGUCHI	10. 03. 23
			DRAWN	TU. TANIGUCHI	10. 03. 23
			Note QT:Qualification Test AT:Assurance Test X:Applicable Test		
	SPECIFICATION SHEET		PART NO.	DH40-37S	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL244-0055-3-00	 1/1