

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△	2	RE - F - 08696	S.K	R-7	03.03.12	△			
△					△				

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-55°C TO 85°C	STORAGE TEMPERATURE RANGE	-10°C TO 50°C (PACKED CONDITION)
	VOLTAGE	30V AC	OPERATING OR STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 90 % MAX. (NOT DEWED)
	CURRENT	0.3A	APPLICABLE CABLE	t=0.20±0.03mm, GOLD PLATING

SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING	CONFIRMED VISUALLY.		×	×
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	AC 20mV MAX., 1mA.	100mΩ MAX. INCLUDING FPC BULK RESISTANCE (L=12mm, THICKNESS OF COPPER FOIL: 35 μm)	×	×
INSULATION RESISTANCE	100V DC.	50 MΩ MIN.	×	×
VOLTAGE PROOF	90V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	×	×
MECHANICAL CHARACTERISTICS				
FPC INSERTION FORCE △	MEASURED BY APPLICABLE FPC. (THICKNESS OF FPC SHALL BE t=0.20mm AT INITIAL CONDITION.)	0.15N/PIN MAX. (CONNECTOR, FPC AT INITIAL CONDITION)	×	—
FPC RETENSION FORCE △	MEASURED BY APPLICABLE FPC. (THICKNESS OF FPC SHALL BE t=0.20mm AT INITIAL CONDITION.)	0.30N/PIN MIN. (CONNECTOR, FPC AT INITIAL CONDITION)	×	—
MECHANICAL OPERATION	10 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 100 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
VIBRATION	FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75mm, — m/s ² FOR 10 CYCLES IN 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 100 mΩ MAX.	×	—
SHOCK	981m/s ² , DURATION OF PULSE 6 ms AT 3 TIMES IN 3 DIRECTIONS.	③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 °C, RELATIVE HUMIDITY 90 TO 95%, 96h.	① CONTACT RESISTANCE: 100 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
DAMP HEAT, CYCLIC	EXPOSED AT -10 TO +65°C, RELATIVE HUMIDITY 90 TO 96%, 10 CYCLES, TOTAL 240 h.	① CONTACT RESISTANCE: 100 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
REMARKS				
		DRAWN S. OKAMURA 02.11.11	DESIGNED S. OKAMURA 02.11.11	CHECKED R. TAKAYASU 02.11.11
		APPROVED M. ISHIDA 02.11.12	RELEASED	
Unless otherwise specified, refer to JIS C 5402.				
Note QT: Qualification Test AT: Assurance Test ×: Applicable Test				
 HIROSE ELECTRIC CO., LTD.		SPECIFICATION SHEET		PART NO. FH23 - *S - 0.3SHW(05)
CODE NO. (OLD) CL	DRAWING NO. ELC4 - 153547 - 01	CODE NO. CL 586		1/2

TO
NC

SPECIFICATIONS						
ITEM	TEST METHOD	REQUIREMENTS	QT	AT		
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→+15TO+35→+85→+15TO+35°C TIME 30→ 2~3 → 30→ 2~3 min. UNDER 5 CYCLES.	① CONTACT RESISTANCE: 100 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—		
DRY HEAT	EXPOSED AT 85 °C, 96 h.	① CONTACT RESISTANCE: 100 mΩ MAX.	×	—		
COLD	EXPOSED AT -55°C, 96 h.	② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—		
CORROSION SALT MIST	EXPOSED AT 35°C, 5% SALT WATER SPRAY FOR 96h.	① CONTACT RESISTANCE: 100 mΩ MAX.	×	—		
HYDROGEN SULPHIDE [JIS C 0092]	EXPOSED AT 40°C, RELATIVE HUMIDITY 80%, 10 ~ 15 PPM FOR 96h.	② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—		
SURPHUR DIOXIDE [JIS C 0090]	EXPOSED AT 40 °C , RELATIVE HUMIDITY 80%, 25 PPM FOR 96 h.	③ NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	×	—		
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING : PEAK TMP. 250°C MAX. REFLOW TMP. 230°C MIN FOR 60 sec. 2) SOLDERING IRONS : TMP. 350±5°C FOR 5 sec .	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	×	—		
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 235°C FOR IMMERSION DURATION, 2 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	×	—		
REMARKS		DRAWN S.OKAMURA 02.11.11	DESIGNED S.OKAMURA 02.11.11	CHECKED R.TAKAYASU 02.11.11	APPROVED M.ISHIDA 02.11.12	RELEASED
Unless otherwise specified, refer to JIS C 5402.						
Note QT:Qualification Test AT:Assurance Test ×:Applicable Test						
 HIROSE ELECTRIC CO., LTD.		SPECIFICATION SHEET		PART NO. FH23 – *S – 0.3SHW(05)		
CODE NO.(OLD) CL	DRAWING NO. ELC4 – 153547 – 01	CODE NO. CL 586			2	