

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾
	VOLTAGE	100 V AC		OPERATING HUMIDITY RANGE	40 % TO 80 %
	CURRENT	0.5 A		STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	×
MARKING		CONFIRMED VISUALLY.			×
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).		40 mΩ MAX.	×
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV MAX, 1 mA(DC OR 1000Hz)		50 mΩ MAX.	×
INSULATION RESISTANCE		250 V DC		100 MΩ MIN.	×
VOLTAGE PROOF		300 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	×
MECHANICAL CHARACTERISTICS					
MATING AND UNMATING FORCES		MEASURED BY APPLICABLE CONNECTOR.		INSERTION FORCE : (0.88 × **) N MAX. EXTRACTION FORCE : (0.1 × **) N MIN.	×
MECHANICAL OPERATION		100 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×
VIBRATION		FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTION.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			×
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 ~ 95 %, 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 100 MΩ MIN.	×
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +15 ~ +35 → +85 → +15 ~ +35 °C TIME 30 → MAX 5 → 30 → MAX 5 min UNDER 5 CYCLES.		③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO HEAVY CORROSION.	×
HYDROGEN SULPHIDE		EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD: JEIDA-38)			×
RESISTANCE TO SOLDERING HEAT		1) REFLOW SOLDERING : 250 °C MAX, : 220 °C MIN, FOR 60 s 2) SOLDERING IRONS : 360 °C, FOR 5 s		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	×
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 240 °C, FOR IMMERSION DURATION, 3 sec..		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	×
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.			APPROVED	HS. OKAWA	05.07.23
			CHECKED	HS. OZAWA	05.07.23
			DESIGNED	TH. NODA	05.07.23
Unless otherwise specified, refer to MIL-STD-1344.			DRAWN	AK. SUZUKAWA	05.07.23
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-071178-25
HRS	SPECIFICATION SHEET		PART NO.	FX6-*S-0.8SV2(71)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.		△ 1/1