

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾	OPERATING HUMIDITY RANGE	40 TO 80 % MAX ⁽³⁾	
	VOLTAGE	100 V AC	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾	
	CURRENT	0.4 A	STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING		CONFIRMED VISUALLY.		×	×
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz)	45 mΩ MAX .	×	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV MAX, 1 mA (DC or 1000Hz)	55 mΩ MAX.	×	—
INSULATION RESISTANCE		250 V DC.	100 MΩ MIN.	×	—
VOLTAGE PROOF		300 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	×	×
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.	1) CONTACT RESISTANCE: 55 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
VIBRATION		FREQUENCY 10 TO 55 TO 10 Hz, SINGLE AMPLITUDE: 0.75 mm, AT 2 h FOR 3 DIRECTIONS.	1) NO ELECTRICAL DISCONTINUITY OF 1 μs. 2) CONTACT RESISTANCE: 55 mΩ MAX. 3) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 BOTH AXIAL DIRECTIONS.		×	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	1) CONTACT RESISTANCE : 55 mΩ MAX. 2) INSULATION RESISTANCE: 100 MΩ MIN.	×	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE: -55 → +85 °C TIME : 30 → 30 min. UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN 2 TO 3 min)	3) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	1) CONTACT RESISTANCE : 55 mΩ MAX. 2) NO HEAVY CORROSION.	×	—
HYDROGEN SULPHIDE		EXPOSED 3 ppm FOR 96 h. (TEST STANDARD: JEIDA-38)		×	—
RESISTANCE TO SOLDERING HEAT		1) REFLOW SOLDERING: PEAK TMP : 250 °C MAX REFLOW TMP: 220 °C MIN FOR 60sec 2) SOLDERING IRONS: 360 °C MAX FOR 5 sec.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINAL.	×	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE 240 ± 3 °C FOR IMMERSION DURATION, 3 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSSED.	×	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARKS (1) TEMPERATURE RISE INCLUDED WHEN ENERGIZED. (2) THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED. (3) NON-CONDENSING. Unless otherwise specified, refer to IEC-60512.			APPROVED	NH. NAKATA	16.11.21
			CHECKED	HT. YAMAGUCHI	16.11.21
			DESIGNED	MT. ITANO	16.11.21
			DRAWN	MT. ITANO	16.11.21
Note QT: Qualification Test AT: Assurance Test X: Applicable Test			DRAWING NO.		ELC-150564-91-00
HRS	SPECIFICATION SHEET		PART NO.	FX8-60P-SV (91)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL578-0001-6-91	△ 1/1