

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-25 °C TO +85 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C	
	_____	_____	_____	_____	
	_____	_____	APPLICABLE CABLE	ϕ 8±0.5 mm	
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	
MARKING		CONFIRMED VISUALLY.		X	X
				—	—
ENVIRONMENTAL CHARACTERISTICS					
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 500 h.		NO HEAVY CORROSION.	
SEALING ⁽¹⁾		EXPOSED AT A DEPTH OF 1.8 m FOR 48h.		NO WATER PENETRATION INSIDE CONNECTOR.	
AIRTIGHTNESS ⁽¹⁾		APPLY AIR PRESSURE 18 kPa FOR 30s TO INSIDE CONNECTOR		NO AIR BUBBLES INSIDE CONNECTOR	