


May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTES. 1. APPLICABLE CABLE.

VINYL SEATH	($\phi 5$)	DRAIN WIRE	WIRE	INSULATOR OUTER DIAMETER 0.90 TO 1.00 DIA. CONDUCTOR SIZE(STRANDED) AWG 26-27 OR EQUIVALET.
FILLER		WIRE	VINYL SEATH OUTER DIAMETER	$\phi 5.0$ *(1)
CONDUCTOR		INSULATOR	DRAIN WIRE	AWG 25 OR EQUIVALET 7/0.18 DIA. *(2)
		SHIELD		

*(1) CABLE ENTRY IS 5.6 MIN.

*(2) CONSTRUCTION IS FOR REFERENCE.

HOOD (2:1)

ADAPTER

- 2 ADAPTER SHALL BE USED TO ALIGN INDIVIDUAL WIRE.
- 3. THE DIMENSION IN PARENTHESIS IS FOR REFERENCE.

HRS DRAWING FOR REFERENCE

2	PHOSPHOR BRONZE	CONTACT: GOLD PLATING 1.27 μ m min TERMINAL: GOLD PLATING 0.03 μ m min UNDER: NICKEL PLATING 2 μ m min	5	POLYCARBONATE	BLACK		
1	POLYCARBONATE	TRANSPARENCY	4	POLYCARBONATE	TRANSPARENCY		
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS		
UNITS		SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm		4 : 1	4	DIS-E-00010343	KIM JAEHYEON	KG. OKITA	20220706
		APPROVED : HO. MIWA	20051017	DRAWING NO. EDC3-120681-01			
HIROSE ELECTRIC CO., LTD.		CHECKED : YH. ENAMI	20051014	PART NO. TM11AP1-88P(C03)			
		DESIGNED : TU. TANIGUCHI	20051014	CODE NO. CL0222-2782-1-03			
		DRAWN : YK. SATO	20050907				

図枠変更