

Part No.	Cable color
~088*1PD~	GRAY
~088*2PD~	BLACK

NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.


2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3 Connector rotation angle is within ± 45 degree from the above image.
For long length in the case of $L > 500$, the angle is optional.

4. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



1	U.FL-LP-088HF(06)	CL331-0560-8-06	2	1.37 Low Loss Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

HALOGEN FREE

UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HRS HIROSE ELECTRIC CO., LTD.		APPROVED	・NK. NINOMIYA	20181214	DRAWING NO.	UFL-2LPHF6-088**PD-A-L 1
		CHECKED	・MT. KANEKO	20181213	PART NO.	
		DESIGNED	・MS. MATSUMOTO	20181213	CODE NO.	
		DRAWN	・MS. MATSUMOTO	20181213	NO.	