




NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.


2 Tolerance for 【L】

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3 Connector rotation angle is within ± 45 degree from the above image.
For long length in the case of $L > 500$, the angle is optional.

4. Specifications are subject to change without notice.

【DIMENSIONS OF CONNECTOR】



For stable supply of this series,
material supplier of piece part#1
will be changed during 2019-2022.
Please note this change in advance.
There will be no difference in product
performance and quality.

2	E. FL CONTACT	CL331-0411-8-11		
1	E. FL-LP-040(01)	CL331-0401-4-01	3	0.81Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

UNITS mm	SCALE FREE	COUNT 1	DESCRIPTION OF REVISIONS DIS-D-00004640	DESIGNED MK. INOUE	CHECKED NK. NINOMIYA	DATE 20200108
HRS HIROSE ELECTRIC CO., LTD.			APPROVED :NK. NINOMIYA 20180608	DRAWING NO.		
			CHECKED :MT. KANEKO 20180608	PART NO.		
			DESIGNED :MS. MATSUMOTO 20180608	CODE NO.		
			DRAWN :MS. MATSUMOTO 20180608	E. FL-2LP-04-A-L		