




May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

REFERENCE DRAWING





2> DRAWING FOR PACKING(No scale)



△數 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 B Y	檢圖 CHKD	年月日 DATE	△數 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 B Y	檢圖 CHKD	年月日 DATE
△					△				
△					△				
△					△				

RECOMMENDED LAND PATTERN DIMENSION OF P.C.B
(P.C.B THICKNESS : t = 1.6mm)



- 1. Lead co-planarity is 0.10mm MAX.
- 2> This is packaged in tray. (30pcs/tray)
- 3> Floating range of this connector is ±0.8mm MAX.
- 4> It shows the vacuum pickup area. Remove the CAP before mating connectors.
- 5. Blemish and hit mark can be occurred through out the manufacturing process which doesn't affect quality level.
- 6. The dimensions in parentheses are for references.
- 7> Please use the connectors within the specified PCB distance.

3	METAL HOLD DOWN	COPPER ALLOY	NiP+SnP	7	CAP	PA	(CAP FOR VACUUM PICKUP)
2	SHIELD	COPPER ALLOY	NiP	6	TRAY	POLYSTYRENE	(TRAY)
1	CASE(A)	LCP	BLACK / UL94-0	5	MF CONTACT	COPPER ALLOY	NiP+AuP(SMT, CONTACT AREA)
NO.	PART	MATERIAL	FINISH,REMARKS	NO.	PART	MATERIAL	FINISH,REMARKS
TITLE				DRAWN	DESIGNED	CHECKED	APPROVED
				J.H.PARK	J.H.PARK	W.S.YOON	B.H.AN
				19.08.23	19.08.23	19.08.23	19.08.23
				RELEASED			
				ENG 20.04.01 DEPT			
DRAWING NO. EDC3-632773				PART NO. KP27F-170S/4-0.5SV(800)			
SCALE 2:1				CODE NO 6547-0012-4-800			
UNITS mm				1/1			