



訂正事項			檢査			年月日			訂正事項			檢査			年月日					
△數	DISCRIPTION	OF REVISIONS	B	Y	CHKD	DATE	△數	DISCRIPTION	OF REVISIONS	B	Y	CHKD	DATE	△數	DISCRIPTION	OF REVISIONS	B	Y	CHKD	DATE
△							△							△						
△							△							△						
△							△							△						

RECOMMENDED PCB LAYOUT (Top-View)



MATING FIGURE



NOTE

- LEAD CO-PLANARITY SHALL BE 0.1mmMAX
- 1REEL : 800EA CONNECTORS

- UL(File No. E132750) AUTHORIZATION ARTICLE.  
C-UL(File No. E132750) AUTHORIZATION ARTICLE.



3	COPPER ALLOY	CONTACT AREA : GOLD 0.2μm MIN. SMT LEAD : GOLD 0.05μm MIN. UNDER PLATING : NICKEL 1μm MIN.	6	CONNECTOR	KW30-2S-2V
2	PHOSPHOR BRONZE	Sn PLATED	5	PET	COVER TAPE
1	LCP	UL94-V0, BLACK	4	PS	EMBOSS CARRIER TAPE
NO.	MATERIAL	FINISH,REMARKS	NO.	MATERIAL	FINISH,REMARKS

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	CHOI 20.06.05 S.W	CHOI 20.06.05 S.W	LIM 20.06.12 S.M	LIM 20.06.12 S.M	

DRAWING NO.	EDC3-633096	PART NO.	KW30-2S-2V (800)
SCALE	5:1	CODE NO.	CL 6669-0017-3-800
UNITS	mm		1/1