

1	APPLICABLE STANDARD		UL:UL1977				
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾		
	VOLTAGE	300 V AC		OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX (NOT DEWED)		
	CURRENT	3 A		STORAGE HUMIDITY RANGE			
UL RATING	VOLTAGE	250 V AC					
	CURRENT	1 A					
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		x	x
MARKING		CONFIRMED VISUALLY.				x	x
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE		100 mA (DC or 1000 Hz).		15 mΩ MAX.		x	—
INSULATION RESISTANCE		500 V DC.		1000 MΩ MIN.		x	—
VOLTAGE PROOF		1000 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		x	—
MECHANICAL CHARACTERISTICS							
MECHANICAL OPERATION		500 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 15 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x	—
VIBRATION		FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTION.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x	—
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				x	—
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.		① CONTACT RESISTANCE: 15 mΩ MAX. ② INSULATION RESISTANCE:1000 MΩ MIN.		x	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-55→+15~+35→+125→+15~+35°C TIME 30 → 10~15 → 30 → 10~15 min UNDER 5 CYCLES.		③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		① CONTACT RESISTANCE: 15 mΩ MAX. ② NO HEAVY CORROSION.		x	—
HYDROGEN SULPHIDE		EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD:JEIDA-38)				x	—
RESISTANCE TO SOLDERING HEAT		1) SOLDER BATH:SOLDER TEMPERATURE, 260±5°C FOR IMMERSION,DURATION,10±1s. 2) SOLDERING IRONS : 360°C FOR 5 s MAX.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.		x	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 245±3°C, FOR IMMERSION DURATION, 2 s.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSSED.		x	—
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED	DATE
1	2	DIS-F-00005942		AK. IWAHORI		HT. YAMAGUCHI	20200313
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.				APPROVED	HT. YAMAGUCHI	20181210	
				CHECKED	HT. YAMAGUCHI	20181210	
				DESIGNED	HR. NAGAYASU	20181207	
				DRAWN	TS. HORI	20181207	
Unless otherwise specified, refer to MIL-STD-202.							
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC-386222-00-00	
HRS	SPECIFICATION SHEET			PART NO.		HIF3H-*PB-2. 54DSA (61)	
	HIROSE ELECTRIC CO., LTD.			CODE NO.		1	1/1