






RECOMMENDED CABLE SUBASSEMBLY


B(FREE)



A-A(20:1)



CABLE TERMINATION FIGURE(20:1)



- NOTES 1. APPLICABLE CABLE: THIN COAXIAL CABLE(AWG#42~AWG#46)
2. THIS CONNECTOR IS NOT HOT PLUGGABLE. MATE AND UNMATE WHILE THE POWER IS OFF.
3. THE ASSEMBLY IS COMPLETED BY COMBINING TWO PARTS(CONNECTOR UNIT, AND METAL SHIELDING). REFER TO THE TABLE FOR EACH ITEM No., PART NAME, PART No. AND CODE No.

ITEM No.	PART NAME	PART No.	CODE No.
1,2	CONNECTOR UNIT	DF38-32P-0.3SD(51)	CL662-4027-4-51
-	METAL SHIELDING	DF38-32P-SHL	CL662-4029-0

1	PHOSPHOR BRONZE	CONTACT AREA : Au PLATING 0.1µm min TERMINATION AREA : Au PLATING 0.1µm min UNDER PLATING : Ni PLATING 1µm min	5	PS	BLACK
			4	POLYESTER	CREAR
			3	PS	CLEAR
			2	LCP	UL94V-0 . BLACK
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE FREE	COUNT △	DESCRIPTION OF REVISIONS	
HIROSE ELECTRIC CO., LTD.		APPROVED : TS. SAKATA	11.09.06	DRAWING NO. EDC3-319521-02	
		CHECKED : HS. OZAWA	11.09.06	PART NO. DF38-32P-0.3SD(51)	
		DESIGNED : TP. MATSUMOTO	11.09.06	CODE NO. CL662-4027-4-51	
		DRAWN : TP. MATSUMOTO	11.09.06	△ 1/2	
		DESIGNED		CHECKED	DATE

