










MATED



RECOMMENDED PATTERN



A-A(10:1)



- NOTES 1 LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1mm MAX.
- 2 WHEN A PART MARKED WITH  HAS A PATTERN BUT NO RESIST ON IT. TAKE CARE TO PREVENT THE CONNECTOR FROM TOUCHING IT.

			6	PS	PLASTIC REEL , BLACK
2	POLYAMIDE (PA6T)	WHITE BEIGE , UL94V-0	5	POLYESTER	CLEAR (COVER TAPE)
1	PHOSPHER BRONZE	CONTACT AREA:GOLD PLATED 0.1µm min	4	A-PET	CLEAR (EMBOSSED CARRIER TAPE)
		LEAD AREA:TIN PLATED 1 µm min UNDER PLATING:NICKEL PLATED 1 µm min	3	PHOSPHER BRONZE	TIN PLATED 1µm min. UNDER PLATING:NICKEL PLATED 1µm min
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm			SCALE 5 : 1		
HRS			COUNT △		
HIROSE ELECTRIC CO., LTD.			DESCRIPTION OF REVISIONS		
			DESIGNED		
			CHECKED		
			DATE		
			APPROVED : KH. IKEDA 08.11.27		
			CHECED : TS. MIYAZAKI 08.11.27		
			DESIGNED : TY. YAMASAKI 08.11.26		
			DRAWN : TY. YAMASAKI 08.11.26		
			DRAWING NO. EDC3-161884-02		
			PART NO. DF17(2.5)-26DP-0.5V(57)		
			CODE NO. CL683-0245-4-57		
			△ 1/2		

