


Dec.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Part No.	Cable color
~04*1TV~	WHITE
~04*2TV~	BLACK


NOTE 1 We indicate the length of the harness on the last of product name. 'L' part.

2 Tolerance for [ L ]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	$\pm 4$
$200 < L \leq 500$	$\pm 8$
$500 < L \leq 1000$	$\pm 12$
$1000 < L$	$\pm 1.5\%$

3. Specifications are subject to change without notice.

**[ DIMENSIONS OF CONNECTOR ]**



1	X.FL-LP-040(09)	CL331-0700-5-09	2	0.81 Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

HALOGEN FREE

UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
<b>HIROSE ELECTRIC CO., LTD.</b>	APPROVED	•NK. NINOMIYA	20230608	DRAWING NO.		
	CHECKED	•NK. NINOMIYA	20230608	PART NO.		
	DESIGNED	•MK. INOUE	20230608	X.FL-LP9-04**TV-A-L <span style="border: 1px solid black; padding: 2px;">1</span>		
	DRAWN	•MK. INOUE	20230608	CODE NO. <span style="border: 1px solid black; padding: 2px;">1/1</span>		