


Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



| Part No. | Cable color |
|----------|-------------|
| ~04*1TV~ | WHITE |
| ~04*2TV~ | BLACK |


NOTE 1 We indicate the length of the harness on the last of product name. 'L' part.

2 Tolerance for [L]

| Length L [mm] | Tolerance [mm] |
|----------------------|----------------|
| $35 \leq L \leq 200$ | ± 4 |
| $200 < L \leq 500$ | ± 8 |
| $500 < L \leq 1000$ | ± 12 |
| $L > 1000$ | $\pm 1.5\%$ |

3. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



| | | | | |
|-----|-----------------|-----------------|-----|-------------------------|
| 1 | X.FL-LP-040(09) | CL331-0700-5-09 | 2 | 0.81 Dia. coaxial cable |
| NO. | PART NO. | CODE NO. | NO. | PART NO. |

HALOGEN FREE

| UNITS mm | SCALE FREE | COUNT | DESCRIPTION OF REVISIONS | DESIGNED | CHECKED | DATE |
|----------------------------------|---------------|---------------|--------------------------|--|---------|------|
| HIROSE ELECTRIC CO., LTD. | APPROVED | •NK. NINOMIYA | 20230608 | DRAWING NO. | | |
| | CHECKED | •NK. NINOMIYA | 20230608 | PART NO. X.FL-LP9-04**TV-A-L 1 | | |
| | DESIGNED | •MK. INOUE | 20230608 | CODE NO. | | |
| | DRAWN | •MK. INOUE | 20230608 | <div style="display: flex; align-items: center;"> 1 1 </div> | | |