

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C(NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C(NOTES 3)		
	OPERATING HUMIDITY RANGE	20% TO 80%(NOTES 2)	STORAGE HUMIDITY RANGE	40% TO 70%(NOTES 2)(NOTES 3)		
	VOLTAGE		APPLICABLE CONNECTOR	DF81※-40S-0.4H(##)		
	CURRENT		APPLICABLE CABLE			
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QTAT	
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	XX	
MARKING		CONFIRMED VISUALLY.			XX	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
△						
REMARKS			APPROVED	TS. SAKATA	12. 11. 12	
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT						
NOTE2: NON CONDENSING				CHECKED	HS. OZAWA	12. 11. 12
NOTE3: THE TERM "STORAGE" REFERS TO PRODUCTS STORED FOR A LONG PERIOD PRIOR TO MOUNTING AND USE. THE OPERATING TEMPERATURE AND HUMIDITY RANGE COVERS THE NON-CONDUCTING CONDITION OF CONNECTORS AFTER BOARD MOUNTING AND THE TEMPORARY STORAGE CONDITIONS OF TRANSPORTATION, etc				DESIGNED	AH. MIYAZAKI	12. 11. 09
Unless otherwise specified, refer to JIS C 5402,IEC60512.				DRAWN	AH. MIYAZAKI	12. 11. 09
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC4-345355-01		
HRS	SPECIFICATION SHEET		PART NO.	DF81-40P-LCH		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL662-8109-9-00	△1/1	