
Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Part No.	Cable color
~04*1TV~	WHITE
~04*2TV~	BLACK

△1

NOTE 1 We indicate the length of the harness on the last of product name. 'L' part.

2 Tolerance for [L]


Length L [mm]	Tolerance [mm]
35 ≦ L ≦ 200	±4
200 < L ≦ 500	±8
500 < L ≦ 1000	±12
1000 < L	±1.5%

3 Connector rotation angle is within ±45 degree from the above image.
For long length in the case of L>500, the angle is optional.

4. Specifications are subject to change without notice.

HRS DRAWING FOR REFERENCE

【DIMENSIONS OF CONNECTOR】



1	W.FL2-LP-040HF(06)	CL331-0311-3-06	2	0.81 Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

HALOGEN FREE

UNITS mm	SCALE FREE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		△1	1	DIS-D-00003244	MS. MATSUMOTO	MT. KANEKO	18.06.14

HIROSE ELECTRIC CO., LTD.

APPROVED	NK. NINOMIYA	16.07.26
CHECKED	MT. KANEKO	16.07.26
DESIGNED	MS. MATSUMOTO	16.07.26
DRAWN	MS. MATSUMOTO	16.07.26

DRAWING NO.
PART NO. WFL2-2LPHF6-04**TV-A-L 1
CODE NO. △1 1/1

FORM HC0011-5-51