

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.





2> APPLICATION PATTERN



1> (DELETE 6 ITEM IN THE TABLE)


PART NO.	HRS NO.	CONTACTS	A	B	C	D	E
DF14A- 4P-1.25H(35)	CL538-0035-9-35	4	9.95	3.75	5.45	6.15	10.55
DF14A- 6P-1.25H(35)	CL538-0037-4-35	6	12.45	6.25	7.95	8.65	13.05
DF14A-10P-1.25H(35)	CL538-0041-1-35	10	17.45	11.25	12.95	13.65	18.05
DF14A-15P-1.25H(35)	CL538-0114-3-35	15	23.70	17.50	19.20	19.90	24.30
DF14A-20P-1.25H(35)	CL538-0119-7-35	20	29.95	23.75	25.45	26.15	30.55
DF14A-25P-1.25H(35)	CL538-0124-7-35	25	36.20	30.00	31.70	32.40	36.80
DF14A-30P-1.25H(35)	CL538-0045-2-35	30	42.45	36.25	37.95	38.65	43.05







HRS DRAWING FOR REFERENCE

3> RECOMMENDED PATTERN





1> (DELETED)



NOTE 1. LEAD CO-PLANALITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1 MAX.
2> WHEN THIS CONNECTOR MATES WITH DF14-*S-1.25C , THE MATTING LENGTH IS 7.3mm.
3> RECOMMENDED METAL MASK THICKNESS:0.15mm
OPEN AREA RETIO:100%

NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
3	PHOSPHOR BRONZE	TIN PLATED 1μm min UNDER PLATING:NICKEL PLATED 1μm min	5	ELASTOMER	GREEN
2	BRASS	TIN PLATED 1μm min UNDER PLATING:NICKEL PLATED 1μm min	4	R.PVC	ELECTROSTATIC PROTECTION, CLEAR
1	POLYAMIDE	BEIGE, UL94V-0			


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	1>	3	DIS-H-00007014	HK.HAYASHI	TS.KUMAZAWA	20201211

HIROSE ELECTRIC CO., LTD.

APPROVED	HS.OKAWA	20200330
CHECKED	TS.KUMAZAWA	20200330
DESIGNED	HK.HAYASHI	20200330
DRAWN	DS.HIROWATARI	20200326


DRAWING NO.	EDC-160309-35-00
PART NO.	DF14A-*P-1.25H(35)
CODE NO.	CL538- 1> 1/2

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS DRAWING FOR REFERENCE

A−A (10:1)



△1 (DELETE 6 ITEM IN THE TABLE)

PART NO.	CONTACTS	QUANTITY OF CONNECTTOR
DF14A-4P-1.25H(35)	4	49
DF14A-6P-1.25H(35)	6	39
DF14A-10P-1.25H(35)	10	28
DF14A-15P-1.25H(35)	15	20
DF14A-20P-1.25H(35)	20	16
DF14A-25P-1.25H(35)	25	13
DF14A-30P-1.25H(35)	30	11

NOTE 4 THE TUBE HAS ONE STOPPER AT EACH END.
5 WARPAGE OF THE TUBE SHALL BE ALLOWED ±2mm PER 510mm.
6 MINIMUM UNIT OF PURCHASE SHALL BE THE QUANTITY OF CONNECTORS IN TUBE.

DRAWING NO.	EDC-160309-35-00
PART NO.	DF14A-*P-1.25H(35)
CODE NO.	CL538- △1 2/2