


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




RECOMMENDED LAND PATTERN DIMENSION OF PCB
(RECOMMENDED METAL MASK THICKNESS:0.15mm)




HRS DRAWING FOR REFERENCE

NOTES
1. SMT LEAD-COPLANARITY:0.1 MAX.
2. THIS PRODUCT HAS NO POLARITY TO PATTERN FOR MOUNTING.
3. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
4. STACKING HEIGHT FROM LEAD TO LEAD(REFERENCE DIMENSIONS)
5. BOARD DISTANCE
6. AREA IS VACUUM PICKUP AREA FOR REFERENCE.

| NO. | MATERIAL | FINISH , REMARKS | NO. | MATERIAL | FINISH , REMARKS |
|---|---|---|---|---|---|
| 3 | COPPER ARROY | CONTACT AREA:GOLD 0.76μm min. | 6 | PET | TOP COVER TAPE |
| | | LEAD AREA:GOLD 0.03μm min. | 5 | PS | EMBOSSED CARRIER TAPE |
| | | UNDER PLATING:NICKEL 1.3μm min. | 4 | COPPER ARROY | SURFACE AREA:GOLD 0.03μm min. |
| 1, 2 | LCP | BEIGE UL94V-0 | | | UNDER PLATING:NICKEL 1.3μm min. |


| UNITS | SCALE | | COUNT | DESCRIPTION OF REVISIONS | DESIGNED | CHECKED | DATE |
|---|---|---|---|---|---|---|---|
| mm | 4 : 1 | △ | | | | | |

HIROSE ELECTRIC CO., LTD.


| | | | |
|---|---|---|---|
| APPROVED | HS. OKAWA | 11. 03. 24 | DRAWING NO. EDC3-330879-01 |
| CHECKED | KI. HIROKAWA | 11. 03. 24 | PART NO. FX10A-168P-SV2(83) |
| DESIGNED | DK. AIMOTO | 11. 03. 23 | CODE NO. CL570-0302-1-83 |
| DRAWN | DK. AIMOTO | 11. 03. 23 | △ 1/2 |

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demands high reliability, kindly contact our sales window correspondents.


# DRAWING FOR PACKING(2:1)




A(5:1)




REELED DIMENSION(FREE)




HRS DRAWING FOR REFERENCE

NOTES 1 1REEL:900 CONNECTORS.
2 MINIMUM 10 COMPARTMENTS FROM BOTH REEL ENDS REMAIN EMPTY.
3 THIS PRODUCT HAS NO POLARITY TO TAPE AND REEL PACKAGING.
4 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

| | | |
|---|---|---|
| HRS | DRAWING NO. | EDC3-330879-01 |
| | PART NO. | FX10A-168P-SV2(83) |
| | CODE NO. | CL570-0302-1-83 △ 2/2 |