

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV. RoHS COMPLIANT





MATED CONNECTOR




RECOMMENDED PCB PATTERN (FREE)
(PCB THICKNESS:t=1.6mm. METAL MASK THICKNESS:t=0.1mm)










NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250℃
OVER 230℃ : 20~40s
PREHEAET : 150~180℃
90~120s

2. TEMPERATURE FOR SOLDERING IRON
:280~300℃ WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.10mm.
6. ACCORDING TO THE SOLDERING CONDITIONS, THERE ARE EVENTS WHERE SOLDER DOESN' T GET MOLTEN DUE TO LOW TEMPERATURE OF SOLDERING AREA.
IN SUCH EVENTS, IF REFLOW TEMPERATURE IS RAISED INTENTIONALLY TO GET THE SOLDER MOLTEN, IT MAY CAUSE EXCESSIVE HEAT OF UP TO 250℃ ON THE OUTER (TOP) SURFACE OF CONNECTOR THAT CAN LEAD TO THE OCCURRENCE OF BLISTER.
PLEASE ENSURE THAT TEMPERATURE OF OUTER (TOP) SURFACE OF CONNECTOR SHALL NOT EXCEED 250℃ WHILE SOLDERING.

TEMP(℃)



NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
3	COPPER ALLOY	SURFACE : TIN PLATING 1μm min UNDER : NICKEL PLATING 1μm min	6	POLYESTER	
2	COPPER ALLOY	SURFACE : TIN PLATING 1μm min UNDER : NICKEL PLATING 1μm min	5	POLYSTYRENE	
1	PA	GRAY, UL94V-0	4	BRASS	SURFACE : TIN PLATING 1μm min UNDER : NICKEL PLATING 1μm min

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	△2	1	DIS-T-00019155	YANG CHUAN XING	MH. SHOUJI	20231110

HRS HIROSE ELECTRIC CO., LTD.


APPROVED	AH. EDASHIGE	20211026	DRAWING NO. EDC-395655-00-00
CHECKED	AH. EDASHIGE	20211026	PART NO. ZH05-24DS-2H(B)
DESIGNED	KH. MARUNO	20211025	
DRAWN	YANG CHUAN XING	20211025	CODE NO. CL0756-2109-0-00 △2 1/2

HRS DRAWING FOR REFERENCE

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


PACKING STYLE

REEL DIMENSION (FREE)



250 PCS/REEL


PACKING STYLE DRAWING



HRS DRAWING FOR REFERENCE

CARDBOARD DIMENSION (FREE)

W=(405) (mm)
D=(405) (mm)
H=(63) (mm)



DRAWING NO.	EDC-395655-00-00
PART NO.	ZH05-24DS-2H(B)
CODE NO.	CL0756-2109-0-00

△2 2/2