
Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS DRAWING FOR REFERENCE

NOTES
1. APPLICABLE WIRE IS AWG #16～#18.(UL1007.UL1015)
   INSURATION DIAMETER φ3.25mm MAX.
2. APPLICABLE CRIMPING MACHINE AND CRIMPING CONDITIONS
   (CRIMP HEIGHT etc.)WILL BE SPECIFIED ACCORDING TO
   AWG # OR WIRE APPLIED.
3. ONE PACKAGE CONSISTS OF 100 PCS.
⚠1 4. REFER TO ATAI-E3005 FOR CRIMP QUALITY STANDARDS.

NO.	MATERIAL	FINISH , REMARKS
1	COPPER ALLOY	CONTACT AREA : GOLD PLATING 0.2μm min TERMINAL AREA : TIN PLATING 1μm min UNDER PLATEING : NICKEL PLATING 0.3μm min

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	⚠1	1	DIS-E-004910	TY.MIURA	NM.NISHIMATSU	14.01.20

HIROSE ELECTRIC CO., LTD.

APPROVED	RI.TAKAYASU	12.12.11
CHECKED	AH.KODAMA	12.12.11
DESIGNED	TY.MIURA	12.12.10
DRAWN	TY.MIURA	12.12.10

DRAWING NO.	EDC3-128199-00
PART NO.	PS2-1618PCA
CODE NO.	CL236-1051-3-00 ⚠1 1/1