
Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Part No.	Cable color
~04*1TV~	WHITE
~04*2TV~	BLACK

HRS DRAWING FOR REFERENCE

NOTE 1 We indicate the length of the harness on the last of product name. 'L' part.


2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
35 ≦ L ≦ 200	±4
200 < L ≦ 500	±8
500 < L ≦ 1000	±12
1000 < L	±1.5%

3 Connector rotation angle is within ±45 degree from the above image.
For long length in the case of L>500, the angle is optional.

4. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



NO.	PART NO.	CODE NO.	NO.	PART NO.
1	U.FL-LP-040HF	CL331-0557-3	2	0.81 Dia. coaxial cable

HALOGEN FREE

UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		0				

HIROSE ELECTRIC CO., LTD.	APPROVED : NK. NINOMIYA	20201028	DRAWING NO.
	CHECKED : MT. KANEKO	20201027	PART NO. UFL-2LPHF6-04**TV-AE-L 1
	DESIGNED : MS. MATSUMOTO	20201027	
	DRAWN : MS. MATSUMOTO	20201027	CODE NO. 0 1/1

FORM HC0011-5-51