Jun.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Part No.	Cable color
~04*1TV~	WHITE
~04*2TV~	BLACK

HRS DRAWING FOR REFERENCE

NOTE 1 We indicate the length of the harness on the last of product name. 'L' part.

2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
35 ≦ L ≦ 200	±4
200 < L ≦ 500	±8
500 < L ≦ 1000	±12
1000 < L	±1.5%

3 Connector rotation angle is within ±45 degree from the above image.
For long length in the case of L>500, the angle is optional.

4. Specifications are subject to change without notice.

【DIMENSIONS OF CONNECTOR】





NO.	PART NO.	CODE NO.	NO.	PART NO.
1	X.FL-LP-040(09)	CL331-0700-5-09	2	0.81 Dia. coaxial cable

HALOGEN FREE

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	FREE	1	1	DIS-D-00011688	MS. MATSUMOTO	MT. KANEKO	20220502

HIROSE ELECTRIC CO., LTD.

APPROVED	NK. NINOMIYA	20200220
CHECKED	MT. KANEKO	20200219
DESIGNED	MK. INOUE	20200219
DRAWN	MK. INOUE	20200219

DRAWING NO.
PART NO. X.FL-2LP9-04**TV-A-L 1
CODE NO.
1 1/1

FORM HC0011-5-51