Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Part No.	Cable color
~04*1TV~	WHITE
~04*2TV~	BLACK

NOTE 1 We indicate the length of the harness on the last of product name. 'L' part.

2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
35 ≦ L ≦ 200	±4
200 < L ≦ 500	±8
500 < L ≦ 1000	±12
1000 < L	±1.5%

3. Specifications are subject to change without notice.

HRS DRAWING FOR REFERENCE

【 DIMENSIONS OF CONNECTOR 】



NO.	PART NO.	CODE NO.	NO.	PART NO.
1	X.FL-LP-040(09)	CL331-0700-5-09	2	0.81 Dia. coaxial cable

HALOGEN FREE

UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		0				

APPROVED	NK. NINOMIYA	20230608	DRAWING NO.
CHECKED	NK. NINOMIYA	20230608	PART NO. X.FL-LP9-04**TV-A-L 1
DESIGNED	MK. INOUE	20230608	CODE NO. 0 1/1
DRAWN	MK. INOUE	20230608	

HIROSE ELECTRIC CO., LTD.

FORM HC0011-5-51