Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

HRS DRAWING FOR REFERENCE







MATING FIGURE



NOTES
1. LEAD CO-PLANARITY SHALL BE 0.1mm MAX.
2. STIFFENER IS REQUIRED FOR MOUNTING ONTO FPC IN ORDER TO AVOID STRESS BY FPC SLACKING TO MOUNTED CONNECTOR.
2 3 LOT No. INFORMATION IS SHOWN IN THE TABLE.
EXAMPLE:8GFD
→YEAR:2008 MONTH:July DAY:15 LINE No.:4
4. UNMATING SHALL BE DONE WITH THE SPECIFIC EXTRACTION TOOL.
5. SOLDERING REWORK IS NOT POSSIBLE SINCE SOLDERING LEADS ARE COVERED BY METAL SHIELDEING.

3

YEAR		MONTH		DAY						LINE No.	
YEAR	CODE	MONTH	CODE	DAY	CODE	DAY	CODE	DAY	CODE	LINE No.	CODE
10	0	Jan	A	1	1	11	B	21	M	1	A
11	1	Feb	B	2	2	12	C	22	N	2	B
12	2	Mar	C	3	3	13	D	23	P	3	C
13	3	Apr	D	4	4	14	E	24	Q	4	D
14	4	May	E	5	5	15	F	25	R	5	E
15	5	Jun	F	6	6	16	G	26	S	6	F
16	6	Jul	G	7	7	17	H	27	T	7	G
17	7	Aug	H	8	8	18	J	28	U	8	H
08	8	Sep	I	9	9	19	K	29	V	9	I
09	9	Oct	J	10	A	20	L	30	W	10	J
		Nov	K					31	X		
		Dec	L								

NO.	MATERIAL	FINISH , REMARKS
6	PS	BLACK
5	POLYESTER	CLEAR
4	PS	CLEAR
3	PHOSPHOR BRONZE	WHOLE AREA : Sn PLATING 1μm min UNDER PLATING : Cu PLATING 0.2μm min
2	LCP	UL94V-0
1	PHOSPHOR BRONZE	CONTACT AREA : Au PLATING 0.3μm min LEAD AREA : Au PLATING 0.1μm min

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	2	3	DIS-H-002943	SI. ISHII	HK. UMEHARA	08. 06. 04

HRS HIROSE ELECTRIC CO., LTD.

APPROVED	TY. OMA	06. 12. 18
CHECED	TS. SAKATA	06. 12. 17
DESIGNED	MN. KENJO	06. 12. 15
DRAWN	MN. KENJO	06. 12. 15

DRAWING NO.	EDC3-313245-01
PART NO.	DF36A-45S-0.4V(51)
CODE NO.	CL662-4008-0-51

2 1/2

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.





STYLE AND DIMENSION OF REEL (FREE)



DETAIL OF PART No. LABEL



HRS DRAWING FOR REFERENCE

RECOMMENDED PATTERN(5:1)



GROUND AREA

RECOMMENDED METAL MASK

THICKNESS: 0.1mm
OPENING RATIO: LEAD AREA 90%
GROUND AREA 100%

7 TAPING (FREE)



NOTES 6. PER REEL: 4000 COMPARTMENTS
7 REFER TO JIS C 0806. (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING)
8. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

DRAWING NO.	EDC3-313245-01
PART NO.	DF36A-45S-0.4V(51)
CODE NO.	CL662-4008-0-51

2 2/2