May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTE 1 We indicate the length of the harness on the last of product name,'L' part.

2 Tolerance for 【L】

L (mm)	STANDARD TOLERANCE
35 ≦L≦ 200	± 4 mm
200 <L≦ 500	± 8 mm
500 <L≦ 1000	± 12 mm
1000 <L	± 1.5% mm

3. Specifications are subject to change without notice.

HRS DRAWING FOR REFERENCE

【DIMENSIONS OF CONNECTOR】



【PRECAUTIONS FOR HANDLING】

◆Connector insertion and extraction

a. Connector shall be extracted vertically by specialised extraction JIG.
Part No. :H.FL-LP-NCCL Code:CL331-0551-7)
Never hold the cable when extracting the cable because it damages the connector.

b. Insert the connector as perpendicularly to the mating surface as possible by aligning the mating axes of both connectors. Do not excessively slant the connectors when inserting.



NO.	PART NO.	CODE NO.	NO.	PART NO.
2	H.FL-LP CONTACT	CL331-0511-2		
1	H.FL-LP-DFS111(01)	CL331-0503-4-01	3	1.5Dia. coaxial cable

UNITS mm	SCALE FREE	△0	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE

HIROSE ELECTRIC CO., LTD.

APPROVED	:NK.NINOMIYA	16.11.08
CHECKED	:NK.NINOMIYA	16.11.08
DESIGNED	:KS.TAKAHASHI	16.11.08
DRAWN	:KS.TAKAHASHI	16.11.08

DRAWING NO.	EDC-373618-00-00
PART NO.	H.FL-LP-111-A-L 1
CODE NO.	CL321-5111-4-00 △0 1/1

FORM HC0011-5-51