

HRS DRAWING FOR REFERENCE

| 1 |             |                                  |           |            | 2           |   |             | 3                                |           |            | 4           |  |  |
|---|-------------|----------------------------------|-----------|------------|-------------|---|-------------|----------------------------------|-----------|------------|-------------|--|--|
|   | △数<br>COUNT | 訂正事項<br>DISCRIPTION OF REVISIONS | 擔當<br>B Y | 檢圖<br>CHKD | 年月日<br>DATE |   | △数<br>COUNT | 訂正事項<br>DISCRIPTION OF REVISIONS | 擔當<br>B Y | 檢圖<br>CHKD | 年月日<br>DATE |  |  |
| △ | 2           | RE-6-3479                        | C.H.S     | L.S.M      | 24. 02. 27  | △ |             |                                  |           |            | . . .       |  |  |
| △ |             |                                  |           |            | . . .       | △ |             |                                  |           |            | . . .       |  |  |
| △ |             |                                  |           |            | . . .       | △ |             |                                  |           |            | . . .       |  |  |

0.75 ±0.1

4.6 ±0.15

4 ±0.15

3 ±0.15

1.4 ±0.15

2.7 ±0.15

4 ±0.15

0.92 ±0.15

0.7 ±0.15

4.75 ±0.2

1.9 ±0.15

0.8 ±0.15

0.5 ±0.15

t= 0.12 ±0.05

1

28

30

HRS

参考

1. 1リール当たり2万pcs

△2. 適用可能なケーブル：AWG#28, 30

| NO. | MATERIAL | FINISH,REMARKS | NO. | MATERIAL     | FINISH,REMARKS                                                                         |
|-----|----------|----------------|-----|--------------|----------------------------------------------------------------------------------------|
|     |          |                | 1   | COPPER ALLOY | CONTACT : GOLD PLATING 0.2μm MIN.<br>CARRIER : NICKEL 1μm MIN.<br>OVER NICKEL 1μm MIN. |

| CODE NO. (OLD) | DRAWN                   | DESIGNED                | CHECKED                | APPROVED               | RELEASED |
|----------------|-------------------------|-------------------------|------------------------|------------------------|----------|
|                | CHOI<br>24.02.27<br>H.S | CHOI<br>24.02.27<br>H.S | LIM<br>24.02.27<br>S.M | LIM<br>24.02.27<br>S.M |          |

| DRAWING NO. | PART NO.             |
|-------------|----------------------|
| JDC3-633135 | KW30A-2830PCFA (800) |

| SCALE       | CODE NO            |   |
|-------------|--------------------|---|
| 10:1        | CL 6669-0045-9-800 | 1 |
| UNITS<br>mm |                    | 1 |

HRS

HIROSE KOREA CO.,LTD.