



Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.








PART NO.	HRS NO.	CONTACTS	A	B	C	D	E
DF14A- 2P-1.25H(22)	CL538-0033-3-22	2	7.45	1.25	2.95	3.65	8.05
DF14A- 3P-1.25H(22)	CL538-0034-6-22	3	8.70	2.50	4.20	4.90	9.30
DF14A- 4P-1.25H(22)	CL538-0035-9-22	4	9.95	3.75	5.45	6.15	10.55
DF14A- 5P-1.25H(22)	CL538-0036-1-22	5	11.20	5.00	6.70	7.40	11.80
DF14A- 6P-1.25H(22)	CL538-0037-4-22	6	12.45	6.25	7.95	8.65	13.05
DF14A- 7P-1.25H(22)	CL538-0038-7-22	7	13.70	7.50	9.20	9.90	14.30
DF14A- 8P-1.25H(22)	CL538-0039-0-22	8	14.95	8.75	10.45	11.15	15.55
DF14A- 9P-1.25H(22)	CL538-0040-9-22	9	16.20	10.00	11.70	12.40	16.80
DF14A-10P-1.25H(22)	CL538-0041-1-22	10	17.45	11.25	12.95	13.65	18.05
DF14A-15P-1.25H(22)	CL538-0114-3-22	15	23.70	17.50	19.20	19.90	24.30
DF14A-20P-1.25H(22)	CL538-0119-7-22	20	29.95	23.75	25.45	26.15	30.55
DF14A-25P-1.25H(22)	CL538-0124-7-22	25	36.20	30.00	31.70	32.40	36.80
DF14A-30P-1.25H(22)	CL538-0045-2-22	30	42.45	36.25	37.95	38.65	43.05

















NOTE 1. LEAD CO-PLANALITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1 MAX.
2 WHEN THIS CONNECTOR MATES WITH DF14-*S-1.25C , THE MATTING LENGTH IS 7.3mm.
3 FOR CONNECTORS , 2 OR 3 CONTACTS , SIMPLIFIED LOCK HOLE SHALL BE SET AT THE CENTER OF HOUSING.
4 RECOMMENDED METAL MASK THICKNESS:0.15-0.2mm
OPEN AREA RETIO:100%

NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
3	PHOSPHOR BRONZE	SURFACE:TIN PLATED 1μm min UNDER PLATING:NICKEL PLATED 1μm min	5	POLYESTER	CLEAR(COVER TAPE)
2	BRASS	SURFACE:TIN PLATED 1μm min UNDER PLATING:NICKEL PLATED 1μm min	4	PS	CLEAR (EMBOSSED CARRIER TAPE)
1	POLYAMIDE	BEIGE, UL94V-0			


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	0					


HIROSE ELECTRIC CO., LTD.

APPROVED	HS. OKAWA	20200313	DRAWING NO. EDC-160309-22-00
CHECKED	TS. KUMAZAWA	20200313	PART NO. DF14A-*P-1.25H(22)
DESIGNED	HK. HAYASHI	20200313	CODE NO. CL538- 0 1/2
DRAWN	DS. HIROWATARI	20200306	

HRS DRAWING FOR REFERENCE


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.







PART NO.	CONTACTS	F	G	H	J	K
DF14A- 2P-1.25H(22)	2	7.5	-	16	7.85	16.4
DF14A- 3P-1.25H(22)	3	7.5	-	16	9.1	16.4
DF14A- 4P-1.25H(22)	4	11.5	-	24	10.35	24.4
DF14A- 5P-1.25H(22)	5	11.5	-	24	11.6	24.4
DF14A- 6P-1.25H(22)	6	11.5	-	24	12.85	24.4
DF14A- 7P-1.25H(22)	7	11.5	-	24	14.1	24.4
DF14A- 8P-1.25H(22)	8	11.5	-	24	15.35	24.4
DF14A- 9P-1.25H(22)	9	11.5	-	24	16.6	24.4
DF14A-10P-1.25H(22)	10	11.5	-	24	17.85	24.4
DF14A-15P-1.25H(22)	15	20.2	40.4	44	24.1	44.4
DF14A-20P-1.25H(22)	20	20.2	40.4	44	30.35	44.4
DF14A-25P-1.25H(22)	25	26.2	52.4	56	36.6	56.4
DF14A-30P-1.25H(22)	30	26.2	52.4	56	42.85	56.4

STYLE AND DIMENSION OF REEL





A–A



SUPPLIER
QUANTITY
PART NO.
CODE NO.
DATE OF MANUFACTURED

DETAIL OF PART NO. LABEL

生産月日	年　月　日
CLコード	538-****-*-22
品名	DF14A-*P-1.25H(22)
納入数量	1000個
納入者	ヒロセ電機株式会社

NOTE 5 1 REEL : 1000 CONNECTORS
6 AT THE BEGINING OF THE REEL , 30 COMPONENTS SHALL BE EMPTY .
7 AT THE END OF THE REEL , 20 COMPONENTS SHALL BE EMPTY .
WHEN THE TAPE WIDTH IS 44 TO 56mm , SPROCKET HOLES SHALL
BE SET ON BOTH SIDES OF REEL AS SHOWN ON THIS DRAWING .

HRS DRAWING FOR REFERENCE

DRAWING NO.	EDC-160309-22-00
PART NO.	DF14A-*P-1.25H(22)
CODE NO.	CL538-