




Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

















HRS DRAWING FOR REFERENCE

Notes 1 : Lead co-planality include reinforced metal fittings shall be 0.1mm MAX.
2 If there are pattern and a via hole on ▨ part,
there is a possibility that it will make contact with the leads.

Part No.	Number of Contacts	Code No.	A	B	C
DF13EA-10DP-1.25V(22)	10	CL536-0570-0-22	12.10	5.00	8.70
DF13EA-20DP-1.25V(22)	20	CL536-0571-0-22	18.35	11.25	14.95
DF13EA-30DP-1.25V(22)	30	CL536-0572-0-22	24.60	17.50	21.20

NO.	MATERIAL	FINISH , REMARKS
2	Brass	Surface:Tin plated 1μm min Under plating:Nickel plated 1μm min
1	Polyamide	Beige, UL94V-0


NO.	MATERIAL	FINISH , REMARKS
6	Polyamide	Beige, UL94V-0
5	Polyester	Clear(Cover tape)
4	PS	Clear(Embossed carrier tape)
3	Phosphor bronze	Tin plated 1μm min


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	1	1	DIS-H-00016939	HT.SATO	SZ.ONO	20230127

HIROSE ELECTRIC CO., LTD.

APPROVED	HS.OKAWA	20200313	DRAWING NO. EDC-367982-22-00
CHECKED	TS.KUMAZAWA	20200313	PART NO. DF13EA-*DP-1.25V(22)
DESIGNED	HK.HAYASHI	20200313	CODE NO. CL536- 1/2
DRAWN	DS.HIROWATARI	20200306	


Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.





Part No.	Code No.	Number of contacts	F	G	H	J
DF13EA-10DP-1.25V(22)	CL536-0570-0-22	10	11.5	—	24	24.4
DF13EA-20DP-1.25V(22)	CL536-0571-0-22	20	14.2	28.4	32	32.4
DF13EA-30DP-1.25V(22)	CL536-0572-0-22	30	20.2	40.4	44	44.4


Style and dimension of reel




Notes 3 : 1 REEL 1000 connectors.
4 : At the biginning of the reel, 30 components shall be empty.
At the end of the reel, 20 components shall be empty.
5 When the tape width is 32mm and more over, sprocket holes shall be set on both sides of reel as shown on this drawing.
6 For 10 and 30 contacts cap shall be at the center of component(shown in drawing with continuous line), for 20 contacts at the position moved to HRS marking by half pitch(shown in drawing with dotted line).
7 Detail of part No. label is written in japanese.

HRS DRAWING FOR REFERENCE

L (10 : 1)



M–M



7 Detail of Part NO. label

Supplier
Quantity
Part No.
Code No.
Date of manufactured

生産月日	年　月　日
図番	CL536-****-*-22
品番	DF13EA-*DP-1.25V(22)
納入数量	1000ko
納入者	ヒロセ電機（株）

DRAWING NO.	EDC-367982-22-00
PART NO.	DF13EA-*DP-1.25V(22)
CODE NO.	CL536-

1 2/2