


Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.








1 (DELETE 2 ITEM IN THE TABLE)

PART NO.	HRS NO.	CONTACTS	A	B	C	D	E	F
DF14- 2P-1.25H(65)	CL538-0021-4-65	2	7.45	1.25	2.95	3.65	6.45	8.05
DF14- 4P-1.25H(65)	CL538-0023-0-65	4	9.95	3.75	5.45	6.15	8.95	10.55
DF14- 5P-1.25H(65)	CL538-0024-2-65	5	11.20	5.00	6.70	7.40	10.20	11.80
DF14- 6P-1.25H(65)	CL538-0025-5-65	6	12.45	6.25	7.95	8.65	11.45	13.05
DF14- 8P-1.25H(65)	CL538-0027-0-65	8	14.95	8.75	10.45	11.15	13.95	15.55
DF14- 9P-1.25H(65)	CL538-0028-3-65	9	16.20	10.00	11.70	12.40	15.20	16.80
DF14-10P-1.25H(65)	CL538-0029-6-65	10	17.45	11.25	12.95	13.65	16.45	18.05
DF14-15P-1.25H(65)	CL538-0084-4-65	15	23.70	17.50	19.20	19.90	22.70	24.30
DF14-20P-1.25H(65)	CL538-0089-8-65	20	29.95	23.75	25.45	26.15	28.95	30.55
DF14-25P-1.25H(65)	CL538-0094-8-65	25	36.20	30.00	31.70	32.40	35.20	36.80
DF14-30P-1.25H(65)	CL538-0020-1-65	30	42.45	36.25	37.95	38.65	41.45	43.05











1 (DELETED)





NOTE 1. LEAD CO-PLANALITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1 MAX.
2 WHEN THIS CONNECTOR MATES WITH DF14-*S-1.25C , THE MATTING LENGTH IS 7.3mm.
3 FOR CONNECTORS , 2 CONTACTS , SIMPLIFIED LOCK HOLE SHALL BE SET AT THE CENTER OF HOUSING.
4 RECOMMENDED METAL MASK THICKNESS:0.15mm
OPEN AREA RETIO:100%

NO.	MATERIAL	FINISH , REMARKS
2	BRASS	CONTACT AREA:GOLD PLATED 0.1μm min LEAD AREA:TIN PLATED 1μm min UNDER PLATING:NICKEL PLATED 1μm min
1	POLYAMIDE	BEIGE, UL94V-0

NO.	MATERIAL	FINISH , REMARKS
5	ELASTOMER	GREEN
4	R.PVC	ELECTOROSTATIC PROTECTION, CLEAR
3	PHOSPHOR BRONZE	TIN PLATED 1μm min UNDER PLATING:NICKEL PLATED 1μm min


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	1	3	DIS-H-00007014	HK.HAYASHI	TS.KUMAZAWA	20201211

APPROVED	HS.OKAWA	20200330	DRAWING NO. EDC-160307-65-00
CHECKED	TS.KUMAZAWA	20200330	PART NO. DF14-*P-1.25H(65)
DESIGNED	HK.HAYASHI	20200330	CODE NO. CL538- 1/2
DRAWN	DS.HIROWATARI	20200326	

HIROSE ELECTRIC CO., LTD.


HRS DRAWING FOR REFERENCE

Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS DRAWING FOR REFERENCE

A−A(10:1)



NOTE 5 THE TUBE HAS ONE STOPPER AT EACH END.
6 WARPAGE OF THE TUBE SHALL BE ALLOWED ±2mm PER 510mm.
7 MINIMUM UNIT OF PURCHASE SHALL BE THE QUANTITY OF CONNECTORS IN TUBE.

△1 (DELETE 2 ITEM IN THE TABLE)

PART NO.	CONTACTS	QUANTITY OF CONNECTTOR
DF14-2P-1.25H(65)	2	66
DF14-4P-1.25H(65)	4	49
DF14-5P-1.25H(65)	5	44
DF14-6P-1.25H(65)	6	39
DF14-8P-1.25H(65)	8	32
DF14-9P-1.25H(65)	9	30
DF14-10P-1.25H(65)	10	28
DF14-15P-1.25H(65)	15	20
DF14-20P-1.25H(65)	20	16
DF14-25P-1.25H(65)	25	13
DF14-30P-1.25H(65)	30	11

HRS	DRAWING NO.	EDC-160307-65-00
	PART NO.	DF14-*P-1.25H(65)
	CODE NO.	CL538- △1 2/2