








Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



RECOMMENDED LAND PATTERN DIMENSION OF PCB (MOUNTING SIDE) (2:1)
(RECOMMENDED METAL MASK THICKNESS:0.15mm)




- NOTE 1. LEAD CO-PLANARITY SHALL BE 0.1mm MAX.
2. TUBE PACKAGING SHALL BE APPLIED FOR THIS PRODUCT.
SEE NEXT PAGE FOR DETAILS.
3. FOR MODIFICATION, ETC., PREVENTIVE HOLE FOR SINK
MARK MAY BE ADDED ACCORDING TO CIRCUMSTANCES.
4. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

2	PHOSPHOR BRONZE	CONTACT AREA:GOLD 0.1μm min.								
		LEAD AREA:GOLD 0.03μm min.								
1	PPS	UNDER PLATING:NICKEL 1.5μm min.		4	ELASTOMERS	(STOPPER)				
		LIGHT BROWN (UL94V-0)		3	POLYVINYL CHLORIDE	(TUBE)				
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS				
UNITS mm				SCALE 5 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED :NH. NAKATA		18.02.28		DRAWING NO. EDC-150881-68-00				
		CHECKED :HT. YAMAGUCHI		18.02.28		PART NO. FX8C-60S-SV(68)				
		DESIGNED :TY. EDAGAWA		18.02.28		CODE NO. CL578-0801-2-68				
		DRAWN :MK. INOUE		18.02.22						
						 1/2				

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

DRAWING FOR PACKING(FREE)



NOTE 1. 1 TUBE : 21 CONNECTORS.
2. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

HRS	DRAWING NO.	EDC-150881-68-00		
	PART NO.	FX8C-60S-SV(68)		
	CODE NO.	CL578-0801-2-68		2 2