


Feb.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Part No.	Code No.	A	B	C
DF53-2P-0.6C	CL0668-1013-0-00	2.9	1.8	0.6
DF53-3P-0.6C	CL0668-1014-0-00	3.5	2.4	1.2
DF53-4P-0.6C	CL0668-1015-0-00	4.1	3.0	1.8
DF53-5P-0.6C	CL0668-1016-0-00	4.7	3.6	2.4
DF53-6P-0.6C	CL0668-1017-0-00	5.3	4.2	3.0
DF53-8P-0.6C	CL0668-1018-0-00	6.5	5.4	4.2
DF53-10P-0.6C	CL0668-1019-0-00	7.7	6.6	5.4
DF53-12P-0.6C	CL0668-1020-0-00	8.9	7.8	6.6
DF53-14P-0.6C	CL0668-1021-0-00	10.1	9.0	7.8
DF53-16P-0.6C	CL0668-1022-0-00	11.3	10.2	9.0
DF53-18P-0.6C	CL0668-1023-0-00	12.5	11.4	10.2
DF53-20P-0.6C	CL0668-1024-0-00	13.7	12.6	11.4

- 注 1. Per pack:100 pieces.
- ②. A number of slits varies depending on pin count.
 - 2 slits for 2 to 12 pos. (No.1, No.N)
 - 4 slits for 14 to 20 pos. (No.1, No.4, No.N-3, No.N)
3. This product satisfies halogen free requirements defined as 900 ppm maximum chlorine, 900 ppm maximum bromine, and 1500 ppm maximum total of chlorine and bromine.
4. Refer to the technical specification(ETAP-H1051-00) for the packing type.
5. Please make sure refer to the manuals below for operation of this product.
 For cable assembly procedure ETAD-H0995-00
 For operation manual ETAD-H0996-00

	1	PA 9T	BLACK, UL94V-0				
	NO.	MATERIAL	FINISH	REMARKS			

UNITS mm	◎	SCALE 10:1	COUNT 0	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE 2023.03.29
HIROSE ELECTRIC CO., LTD.		APPROVED : SJ. OKAMURA 2024.06.21		DRAWING NO. EDCX-407144-00-00			
		CHECKED : SJ. OKAMURA 2024.06.21		PART NO. DF53-P-0.6C			
		DESIGNED : JN. TONAI 2024.06.21		CODE NO. CL0010-0636-0-00			
		DRAWN : JN. TONAI 2024.06.21		1			