




Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.















HRS DRAWING FOR REFERENCE

NOTES 1 LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1mm MAX.

□ 2 WHEN A PART MARKED WITH ▨ HAS A PATTERN BUT NO RESIST ON IT. TAKE CARE TO PREVENT THE CONNECTOR FROM TOUCHING IT.

MATED



MATED HIGHT(h) (mm)

HEADER No. \ RECEPTACLE No.	DF17#(3.0)-80DS-0.5V(57)	DF17#(4.0)-80DS-0.5V(57)
DF17(2.5)-80DP-0.5V(57)	5.5	6.5

NO.	MATERIAL	FINISH , REMARKS
2	POLYAMIDE (PA6T)	WHITE BEIGE , UL94V-0
1	PHOSPHER BRONZE	CONTACT AREA:GOLD PLATED 0.1μm min LEAD AREA:TIN PLATED 1 μm min UNDER PLATING:NICKEL PLATED 1 μm min


NO.	MATERIAL	FINISH , REMARKS
6	PS	PLASTIC REEL , BLACK
5	POLYESTER	CLEAR (COVER TAPE)
4	A-PET	CLEAR (EMBOSSED CARRIER TAPE)
3	PHOSPHER BRONZE	TIN PLATED 1μm min. UNDER PLATING:NICKEL PLATED 1μm min


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	△					

HIROSE ELECTRIC CO., LTD.


APPROVED	KH. IKEDA	08.11.27	DRAWING NO. EDC3-161802-04
CHECED	TS. MIYAZAKI	08.11.27	PART NO. DF17(2.5)-80DP-0.5V(57)
DESIGNED	TY. YAMASAKI	08.11.26	CODE NO. CL683-0168-5-57
DRAWN	TY. YAMASAKI	08.11.26	△ 1/2

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.






STYLE AND DIMENSION OF REEL (FREE)



DETAIL OF PART NO. LABEL

生産月日	年　月　日
図　番	CL683-0168-5-57
品　名	DF17(2.5)-80DP-0.5V(57)
納入数量	1000 Ko
納入者	ヒロセ電機(株)

C-C



NOTES 3：1 REEL：1000 CONNECTORS.
4：AT THE BEGINNING OF THE REEL、30 COMPONENTS SHALL BE EMPTY. AT THE END OF THE REEL、20 COMPONENTS SHALL BE EMPTY.

HRS DRAWING FOR REFERENCE

DRAWING NO.	EDC3-161802-04
PART NO.	DF17(2.5)-80DP-0.5V(57)
CODE NO.	CL683-0168-5-57 △ 2/2