Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Part No.	Cable color
~068*1T~	GRAY
~068*2T~	BLACK

NOTE 1 We indicate the length of the harness on the last of product name. 'L' part.

2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
35 ≦ L ≦ 200	±4
200 < L ≦ 500	±8
500 < L ≦ 1000	±12
1000 < L	±1.5%

3 Connector rotation angle is within ±45 degree from the above image.
For long length in the case of L>500, the angle is optional.

4. Specifications are subject to change without notice.

HRS DRAWING FOR REFERENCE

【DIMENSIONS OF CONNECTOR】



1	U.FL-LP-068HF	CL331-0566-4	2	1.13 Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

HALOGEN FREE

UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		0				

HIROSE ELECTRIC CO., LTD.	APPROVED : TS. NOBE	18.06.19	DRAWING NO.
	CHECKED : MT. KANEKO	18.06.19	PART NO. U.FL-2LPHF6-068**T-A-L 1
	DESIGNED : MS. MATSUMOTO	18.06.19	
	DRAWN : MS. MATSUMOTO	18.06.19	CODE NO. 0 1/1