



Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.







RECOMMENDED METAL MASK THICKNESS:120μm
RECOMMENDED MASK OPENING RATIO:80% FOR LEAD PAD





A-A
(20:1)





NOTES 1. ALL LEADS METAL FITTINGS CO-PLANARITY SHALL BE 0.1mm MAX.
2 IS NON-CONDUCTIVE AREA.
1 3 THERE IS A POSSIBILITY THAT THE RESIN WILL BE EXPOSED AT THIS AREA, BUT THIS WILL NOT AFFECT THE CONTACT RELIABILITY.

NO.	MATERIAL	FINISH . REMARKS
2	PHOSPHOR BRONZE	CONTACT AREA:Au 0.05μm MIN
		SMT LEAD:Au 0.05μm MIN
		UNDERPLATING:NICKEL 1μm MIN
1	LCP	BLACK, UL94V-0

NO.	MATERIAL	FINISH . REMARKS
7	PS	CLEAR(REINFORCEMENT COLLAR)
6	PS	BLACK(PLASTIC REEL)
5	POLYESTER	CLEAR(COVER TAPE)
4	PS	CLEAR(EMBOSSED CARRIER TAPE)
3	PHOSPHOR BRONZE	CONTACT AREA:Au 0.05μm MIN
		SMT LEAD:Au 0.05μm MIN
		UNDERPLATING:NICKEL 1μm MIN

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	10 : 1	1 2	DIS-H-00006346	PAN YIWEI	YK. SATAKE	20200928

HIROSE ELECTRIC CO., LTD.

APPROVED	MO. ISHIDA	20150701
CHECED	TS. MIYAZAKI	20150701
DESIGNED	SH. HOSODA	20150701
DRAWN	KR. AJITO	20150701


DRAWING NO.	EDC-349576-58-01
PART NO.	DF40GB-70DP-0.4V(58)
CODE NO.	CL684-4199-7-58


1 2

HRS DRAWING FOR REFERENCE


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

EMBOSSED CARRIER TAPE PACKAGING(FREE)







STYLE AND DIMENSION OF REEL(FREE)




D-D (FREE)




C-C(FREE)



E(10:1)





NOTES 4. PER REEL 1000 CONNECTORS.
5. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
6 REFER TO JIS C 0806, IEC 60286-3(PACKING OF COMPONENTS FOR AUTOMATIC HANDLING)
7 AFTER PACKAGING, ROLL 2 METERS OF THE REINFORCEMENT COLLAR TO OUTER CIRCUMFERENCE OF TAPE AND REEL POCKET, AND TAPE DOWN AT THE END THE COLLAR.

HRS DRAWING FOR REFERENCE

HRS	DRAWING NO.	EDC-349576-58-01
	PART NO.	DF40GB-70DP-0.4V(58)
	CODE NO.	CL684-4199-7-58

1 2/2